Product data sheet

Specifications





power cable - between servomotor BSH and servodrive - 4 x 4 mm \hat{A}^2 + 2 x 1 mm \hat{A}^2 - 5m

VW3M5103R50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 268.48 USD

Main

| Product Or Component Type | Power cable |
|--|--|
| Accessory / Separate Part Type | Preassembled power cordset |
| Accessory / Separate Part Category | Connection accessory |
| Product Compatibility | Servo motor BMH, 1 7.48 in (190 mm))E IEC 60204-1 Servo motor BMH, 3 8.07 in (205 mm))E IEC 60204-1 Servo motor BSH, 2 5.51 in (140 mm)) Servo motor BSH, 3 5.51 in (140 mm)) Servo motor BSH, 4 5.51 in (140 mm)) |
| Accessory / Separate Part Destination | Between servo motor and servo drive |
| Range Compatibility | Lexium 32 Lexium 15 Lexium 05 |
| Cable Length | 16.40 ft (5 m) |
| Cable Composition | 4 x 4 mm ² + 2 x 1 mm ² |

Complementary

| Electrical Connection | Free end servo drive side Connector - industrial M40 servo motor side |
|-----------------------|--|
| Net Weight | 4.70 lb(US) (2.13 kg) |

Ordering and shipping details

| Category | US1PC5118263 |
|-------------------|---------------|
| Discount Schedule | PC51 |
| Gtin | 3389119207409 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.07 in (7.800 cm) |
| Package 1 Width | 15.16 in (38.500 cm) |
| Package 1 Length | 15.43 in (39.200 cm) |
| Package 1 Weight | 5.63 lb(US) (2.554 kg) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Unit Type Of Package 2 | P06 |
|------------------------------|---------------------------|
| Number Of Units In Package 2 | 30 |
| Package 2 Height | 29.53 in (75.000 cm) |
| Package 2 Width | 23.62 in (60.000 cm) |
| Package 2 Length | 31.50 in (80.000 cm) |
| Package 2 Weight | 199.43 lb(US) (90.460 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
|---------------------------|---|
| Circularity Profile | End of Life Information |
| Environmental Disclosure | Product Environmental Profile |
| China Rohs Regulation | China RoHS declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Reach Regulation | REACh Declaration |