

Product data sheet

Specifications



Connector module, Lexium 32i,
connection for industrial
connectors, EtherCAT, 4 DI sink,
STO

VW3M9206

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 405.30 USD

Main

Range Of Product	Lexium 32i
Product Or Component Type	Connector module
Accessory / Separate Part Category	Connection accessories
Electrical Connection	Industrial connector

Complementary

Product Compatibility	Drive control unit LXM32i EtherCAT
Accessory / Separate Part Destination	Motor BMI with drive control unit Lexium 32i
Range Compatibility	Lexium 32i
Communication Interface	EtherCAT
Input/Output Type	4 discrete inputs
Discrete Input Logic	Sink
Safety Function	STO (safe torque off)
Net Weight	0.49 lb(US) (0.22 kg)

Ordering and shipping details

Category	US1PC5618289
Discount Schedule	PC56
Gtin	3606480610929
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.23 in (8.2 cm)
Package 1 Width	4.53 in (11.5 cm)
Package 1 Length	6.69 in (17.0 cm)
Package 1 Weight	7.76 oz (220.0 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.39 lb(US) (3.353 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance


✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Connections and Schema

Connection of I/O Module for EtherCAT with Industrial Connectors



- (1) IN
(2) OUT

Signal	Meaning
+24VDC	24 V signal power supply
0VDC	Reference potential to +24VDC
DI0	Digital input 0
DI1	Digital input 1
DI2	Digital input 2
DI3	Digital input 3
STO_A	Safety function STO
STO_COM	Reference potential for safety function STO
STO_B	Safety function STO
SHLD	Shield (grounded internally)
Tx+	Ethernet transmit signal +
Tx-	Ethernet transmit signal -
Rx+	Ethernet receive signal +

Signal	Meaning
Rx-	Ethernet receive signal -
NC	Not connected