Product data sheet

Specifications





empty control station - XAP-A - plastic - 4 openings

XAPA2104

! Discontinued on: Oct 20, 2020

! Discontinued

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Empty control station without hinges	
Device Short Name	XAPA	
Product Destination	For Ø 30.5 mm control and signalling units	
Product Front Plate Size	85 x 226 mm	
Usable Depth	3.27 in (83 mm)	
Number Of Cut-Out	4 cut-outs	
Colour Of Base Of Enclosure	Grey	
Colour Of Cover	Grey	
Material	Glass reinforced polyester	
Cable Entry Undrilled		
Device Mounting	Flush	
P Degree Of Protection IP65 IEC 60529 IP69 NF C 20-010 IP69K		
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water	

Complementary

Number Of Vertical Rows	2
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94

Environment

Protective Treatment	TC TH
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class II IEC 60536 Class II NF C 20-030

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 26, 2024 Life Is On Schneider 1

Ordering and shipping details

Category	22475-WALL STATIONS	
Discount Schedule	ount Schedule CS2	
Gtin	3389110313246	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9 cm)
Package 1 Width	5.31 in (13.5 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	24.34 oz (689.9 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov