Product data sheet

Specifications





die-cast empty control station, XAPG, grey, Ø22, 80x130mm front plate, 3 cut-outs

XAPG2203

() Discontinued on: Jun 30, 2022

(!) End-of-service on: Jul 28, 2022

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPG	
Product Destination	For Ø 22 mm control and signalling units	
Product Front Plate Size	80 x 130 mm	
Usable Depth	1.93 in (49 mm)	
Number Of Cut-Out	3 cut-outs	
Colour Of Base Of Enclosure	Grey RAL 7032)	
Colour Of Cover	Grey RAL 7032)	
Material	Zinc alloy	
Product Mounting	Flush mounting	
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010	

Complementary

Number Of Vertical Rows	1
Cable Entry	0.55 in (14 mm) 1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland
Net Weight	1.33 lb(US) (0.605 kg)
Compatibility Code	XAPG

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Gtin	3389118115750
Returnability	No

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15 cm)
Package 1 Width	11.81 in (30 cm)
Package 1 Length	15.75 in (40 cm)
Package 1 Weight	21.34 oz (605 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov