Product data sheet

Specifications





(!) Discontinued

die-cast empty control station - XAPM - Ø 30.5 - zinc alloy - 2 openings

XAPM2602

- ! Discontinued on: Jun 30, 2022
- ! End-of-service on: Jul 28, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	ХАРМ	
Product Destination	For Ø 30.5 mm control and signalling units	
Product Front Plate Size	80 x 130 mm	
Usable Depth	2.93 in (74.5 mm)	
Number Of Cut-Out	2 cut-outs	
Colour Of Base Of Enclosure	Blue	
Colour Of Cover	Blue	
Material	Zinc alloy	
Cable Entry	1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland 0.55 in (14 mm)	
Device Mounting	ting Flush	
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K	

Complementary

Number Of Vertical Rows

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class I IEC 60536 Class I NE C 20-030

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389110313024

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.46 in (8.8 cm)
Package 1 Width	6.22 in (15.8 cm)
Package 1 Length	3.70 in (9.4 cm)
Package 1 Weight	33.86 oz (960 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov