

# Product data sheet

Specifications



## blue light block for head Ø22 integral LED 230...240V faston connector

ZBVM63

⚠ Discontinued on: Jan 29, 2021

⚠ Discontinued

### Main

Range Of Product	Harmony XB5 Harmony XB4
Product Or Component Type	Light block
Device Short Name	ZBV
Sale Per Indivisible Quantity	5
Connections - Terminals	Faston connector 1 x 6.35 mm Faston connector 2 x 2.8 mm
Signalling Type	Steady
Light Source	Protected LED
Bulb Base	Integral LED
Light Block Supply	Direct
Light Source Colour	Blue
[Us] Rated Supply Voltage	230...240 V AC 50/60 Hz

### Complementary

Net Weight	0.04 lb(US) (0.017 kg)
Supply Voltage Limits	195...264 V AC
Current Consumption	14 mA
Service Life	100000 h at rated voltage and 25 °C
Surge Withstand	1 kV IEC 61000-4-5
Mounting Of Block	Front mounting
Electrical Composition Code	M1 M2 M3 M4 M5 M6 M10 MF1 P1 P2 PF1

### Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-40...158 °F (-40...70 °C)
Ip Degree Of Protection	IP20 IEC 60529
Standards	UL 508 JIS C8201-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-5-5 EN/IEC 60947-1 JIS C8201-1
Resistance To Fast Transients	2 kV IEC 61000-4-4
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) IEC 61000-4-2 8 kV in free air (in insulating parts) IEC 61000-4-2
Electromagnetic Emission	Class B IEC 55011
[Us] Rated Supply Voltage	230...240 V

## Ordering and shipping details

Category	22469-PUSHBUTTON,22MM ACCESSORIES-NEW
Discount Schedule	CS2
Gtin	3389110816938
Returnability	No
Country Of Origin	FR

## Contractual warranty

Warranty	18 months
----------	-----------