
# **Product datasheet**

Specifications





# 21M SIDE PANEL PRISMA G IP30

01045

() Discontinued on: Jun 15, 2023

() Discontinued

#### Main

| Range                                 | Prisma                            |
|---------------------------------------|-----------------------------------|
| Range Of Product                      | Prisma G                          |
| Product Or Component Type             | Side panel                        |
| Accessory / Separate Part<br>Category | Enclosure accessory<br>Spare part |
| Range Compatibility                   | Prisma Prisma G enclosure         |
| Installation Description              | Wall-mounted enclosure            |
| Mounting Location                     | Side                              |
| Number Of Vertical Modules [50<br>Mm] | 21                                |

#### Complementary

| Protective Treatment   | Electrophoresis treatment and hot-polymerised polyester epoxy powder |  |
|------------------------|--|--|
| Surface Finish         | Glossy<br>Textured epoxy polyester                                   |  |
| Colour                 | White (RAL 9001)   |  |
| Special Colour Options | Yes  |  |
| Width                  | 200 mm   |  |
| Height                 | 1075 mm  |  |
| Depth                  | 180 mm   |  |
| Net Weight             | 2.22 kg  |  |
| Quantity Per Set       | Set of 1   |  |

#### Environment

| Ip Degree Of Protection | IP30         |
|-------------------------|--------------|
| Ik Degree Of Protection | IK07<br>IK08 |

## **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 5.0 cm  |
| Package 1 Width              | 20.5 cm |

| Package 1 Length             | 113.0 cm |
|------------------------------|----------|
| Package 1 Weight             | 2.4 kg   |
| Unit Type Of Package 2       | P12      |
| Number Of Units In Package 2 | 36       |
| Package 2 Height             | 60.0 cm  |
| Package 2 Width              | 80.0 cm  |
| Package 2 Length             | 120.0 cm |
| Package 2 Weight             | 98.5 kg  |

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)                                  |
|--------------------------|---|
|                          | EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |