# **Product datasheet**

Specifications





# CLASS 2 INSULATING PLATE WIDTH 600/650

03154

() Discontinued on: Apr 13, 2023

(!) Discontinued

#### Main

Range	Prisma	
Range Of Product	Prisma G	
	Prisma P	
Product Or Component Type	Insulating plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
	Prisma Prisma P cubicle	
Installation Description	Floor-standing enclosure - width 600 mm	
	Wall-mounted enclosure - width 600 mm	
	Cubicle - width 650 mm depth 400 mm	
	Pack enclosure - width 555 mm	
Installed Device	Power meters: kilowatt-hour meters - vertical installation	
Poles Description	2 x 4P: kilowatt-hour meters vertical installation	
	3 x 2P: kilowatt-hour meters vertical installation	
Number Of Vertical Modules [50 Mm]	9 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure	
	9 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure	
	9 module(s): kilowatt-hour meters in 650 mm Widecubicle	
	9 module(s): kilowatt-hour meters in 555 mm WidePack enclosure	
	6 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure	
	6 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure	
	6 module(s): kilowatt-hour meters in 650 mm Widecubicle	
	6 module(s): kilowatt-hour meters in 555 mm WidePack enclosure	
Standards	IEC 61439-2	
Product Certifications	ASEFA	

## Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	420 mm
Net Weight	0.66 kg

600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 2P 3 6 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 2P 3 6 600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 9 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 9 650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 2P 3 6 650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 4P 2 9

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	52.0 cm
Package 1 Length	68.0 cm
Package 1 Weight	670.0 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	81.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	28.8 kg

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile