



Main

Range	Prisma
Range of product	Prisma G Prisma P
Product or component type	Insulating plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma G enclosure Prisma P cubicle Prisma Pack 160 enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Installed device	Power meters: kilowatt-hour meters - vertical installation
Poles description	2 x 4P: kilowatt-hour meters vertical installation 3 x 2P: kilowatt-hour meters vertical installation
Number of vertical modules [50 mm]	9 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure 9 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure 9 module(s): kilowatt-hour meters in 650 mm Widecubicle 9 module(s): kilowatt-hour meters in 555 mm WidePack enclosure 6 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure 6 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure 6 module(s): kilowatt-hour meters in 650 mm Widecubicle 6 module(s): kilowatt-hour meters in 555 mm WidePack enclosure
Standards	IEC 61439-2
Product certifications	ASEFA

Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	420 mm
Net weight	0.66 kg
Functional unit	600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 2P 3 6 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 2P 3 6 600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 9 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 9 650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 2P 3 6 650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 4P 2 9 555 mm Pack 160 Pack enclosure power meters kilowatt-hour meters vertical 2P 3 6 555 mm Pack 160 Pack enclosure power meters kilowatt-hour meters vertical 4P 2 9

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	660 g
Package 1 Height	6 cm
Package 1 width	52 cm
Package 1 Length	68 cm
Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Weight	15.84 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product