



# PLAIN DUCT DOOR W300 33M PRISMA G IP30

08284

! Discontinued on: Jun 15, 2023

! Discontinued

#### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G duct
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 3 hinge
Type Of Door	Plain
Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

## Complementary

Installation Description	Floor-standing duct - width 300 mm
Door Opening Side	Reversible
Number Of Locks	3
Door Opening Angle	130 °
Number Of Vertical Modules [50 Mm]	33
Enclosure Material	Handle: polyamide Cover frame: treated sheet steel
Quantity Per Set	Set of 1
Height	1830 mm
Width	300 mm
Depth	33 mm
Net Weight	6.48 kg
Surface Finish	Matt Smooth
Colour	White (RAL 9001)

#### **Environment**

Ik Degree Of Protection IK08 conforming to EN/IEC 62262

Standards	IEC 61439-2 IEC 61439-1
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

# **Packing Units**

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	34.5 cm
Package 1 Length	171.5 cm
Package 1 Weight	7.65 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	30
Package 2 Height	100.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	263.04 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile