

Product datasheet

Specifications



modular digital ammeter iAMP - 230V - 5..5000A

15209

Main

Range	Acti9
Device Short Name	iAMP
Product Or Component Type	Ammeter
Range Compatibility	Prisma Prisma P door Prisma Prisma G door
Network Type	AC 50/60 Hz
Mounting Support	DIN rail

Complementary

Type Of Measurement	Current
[Us] Rated Supply Voltage	230 AC at 50/60 Hz
Power Consumption In Va	0.3 VA
Power Consumption In Va	0.3 VA
9 Mm Pitches	4
Width	36 mm
Height	87 mm
Depth	65 mm
Connections - Terminals	Tunnel type terminal 2 cable(s) 2.5 mm²

Environment

Standards	EN 50081-1 IEC 61010-1 EN 50082-1
Ambient Air Temperature For Operation	-20...50 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.0 cm
Package 1 Length	9.2 cm
Package 1 Weight	180.0 g
Unit Type Of Package 2	S02

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	36
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.836 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Reach Regulation</div>	<div>REACH Declaration</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div>China RoHS declaration</div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>