## **Product datasheet**

Specifications





# Acti9 iIL single indicator light - Red - 110-230 Vac

A9E18320

#### Main

Range Of Product	Acti9
Product Name	Acti9 ilL
Product Or Component Type	Modular pilot ligth
Device Short Name	ilL
[Us] Rated Supply Voltage	110230 V AC at 50/60 Hz 110130 V DC

## Complementary

•	
Indicator Light	1 LED red, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting Mode	Fixed
Mounting Support	Symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary Connection Terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) rigid 2.5 mm <sup>2</sup> Tunnel type terminal 1 cable(s) flexible 0.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible 2.5 mm <sup>2</sup> Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm <sup>2</sup>
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

#### Environment

Standards	IEC 60947-5-1
Ip Degree Of Protection	IP2 IPxx B
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4080 °C

## **Packing Units**

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	37.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	10.000 cm
Package 2 Length	23.000 cm
Package 2 Weight	514.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.046 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

Halogen Free Plastic Parts & Cables Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations