



Cable ends, Linergy TR cable ends, single conductor, red, 1mm², medium size, 5 sets of 200

AZ5CE010

#### Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 200
Cable Cross Section	1 mm²

## Complementary

Cable End Type	Single conductor
Additional Information	Without marker tag holder
Colour	Red
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 18
Bezel Size	Ø 3.5 mm
Tube Diameter	1.7 mm
Length	14 mm
Tube Length	8 mm
Net Weight	0.165 kg

### **Environment**

Product Certifications	UL
Ambient Air Temperature For	-20105 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.4 cm
Package 1 Width	0.4 cm
Package 1 Length	1.4 cm

Package 1 Weight	1 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	13 cm
Package 2 Width	7 cm
Package 2 Length	12.5 cm
Package 2 Weight	1000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	40000
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	40 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations