

Product datasheet

Specifications



Vivace - switch - 1-way - 16 AX 250 V - 3 gangs - white

KB33_1_WE

! Discontinued on: 23 January 2021

! End-of-service on: 24 January 2021

! Discontinued - Service only

Main

Range	Vivace
Product or component type	Switch
Device short name	KB33
Device application	Lighting
Device presentation	Complete mechanism
Additional switch application	Switch

Complementary

Switch function	1-way
Actuator	Rocker
Number of gangs	3 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Surface finish	Glossy
Type of packing	Plastic bag
Quantity per set	1
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	16 AX at 250 V AC, inductive 16 AX at 250 V AC, fluorescent
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	pillar terminal

Terminal identifier	L1 COM L2
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Wire stripping length	12 mm
Width	87 mm
Height	87 mm

Environment

Standards	MS IEC 60669-1 SS 227 IEC 60669-1
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	91 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	860 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8600 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Recommended replacement(s)