# **Product datasheet**

Specifications





# mini Pragma surface enclosure - 1 x 4 modules - smoked door

MIP10104S

! Discontinued on: May 19, 2023

① Discontinued

#### Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	4
Nb Of Horizontal Rows	1
Type Of Door	Smoked
Width	124 mm outside:
Height	198 mm outside:
Depth	95.5 mm outside:

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	8
Total Number Of 18 Mm Modules	4
[In] Rated Current	50 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Without
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

#### **Environment**

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40

Apr 26, 2024 Life Is On Schneider

Ik Degree Of Protection	IK07
Ambient Air Temperature For	-2560 °C

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	12.5 cm
Package 1 Length	19.5 cm
Package 1 Weight	371 g

## **Contractual warranty**

Warranty 18	months
-------------	--------



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations