## **Product datasheet**

Specification





# Horizontal rotating fixing, square 80 mm RAL 7040. For S3CM HMI encl.

NSYCMUCC80

#### Main

Range	Spacial	
Accessory / Separate Part Category	Cable management accessory	
Product Or Component Type	Bent and rotating enclosure fixing	
Device Application	Multi-purpose	
<b>Enclosure Nominal Dimensions</b>	-	
Mounting Location	On enclosure, in horizontal position	
Mounting Support	Option of passing cables through the inside For 80 mm square tube	
Range Compatibility	Spacial Spacial S3CM	
Device Composition	fixing elements 1 rotating fixing	
Quantity Per Set	Set of 1	

## Complementary

Material	Aluminium
Colour	Grey (RAL 7040)
Surface Finish	Epoxy-polyester powder
Fixing Mode	Fixing through the support surface by 4 screws - screw type M8
Operating Angle	310 °
Permanent Permissible Load	6.55 kg
Height	130 mm
Width	210 mm
Depth	210 mm
Diameter	139 mm
Net Weight	4.12 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	21.0 cm
Package 1 Length	21.0 cm

Package 1 Weight	4.112 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	20
Package 2 Height	50.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	82.24 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations