

Bảng thông số sản phẩm

Thông số kỹ thuật



4 THREADED BARS 400A L1400/ LINERGY BS BB

04173

⚠️ **Ngừng sản xuất vào:** 7 thg 6, 2022

⚠️ **Ngừng cung cấp dịch vụ vào:** 9 thg 10, 2023

⚠️ **Ngừng sản xuất**

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Copper busbar
Product Name	Linergy BS
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure
Busbar Description	Flat bar
Quantity Per Set	Set of 4

Complementary

Installation Direction	Vertical, operating position: rear
Installation Description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
[Ui] Rated Insulation Voltage	1000 V
[Ie] Rated Operational Current	400 A
[Ipk] Rated Peak Withstand Current	55 kA
I²t On Activation	625000 kA².s
Busbar Cross Section	32 x 5 mm
Length	1400 mm
Net Weight	8 kg
Type Of Busbar Connection	M6 threaded hole
Connection Pitch	Connection each 25 mm
Support Thickness	5 mm

Environment

Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	15 cm
Package 1 Length	152 cm
Package 1 Weight	8 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Chứng nhận & Tiêu chuẩn

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins