

Bảng thông số sản phẩm

Thông số kỹ thuật



Acti9 - SPN DB - double door - IP30 - 12 ways

A9HESN12

Main

Range	Acti9 enclosures
Device Short Name	SPN
Product Or Component Type	Empty enclosure
Device Application	Low voltage electrical distribution
Type Of Front Cover	Reversible Double door
Enclosure Type	Metal enclosure
Provided Equipment	removable gland plates removable centre plate blanking plate earthing bar comb busbar neutral bar earthing wire DIN rail
Colour	White (RAL 9003)

Complementary

Protection Device Type	Miniature circuit breaker (MCB) 1P 63 A 10 kA outgoer Isolator 2P main incomer Miniature circuit breaker (MCB) 2P main incomer Residual current circuit breaker (RCCB) 2P main incomer Residual current circuit breaker with overcurrent protection (RCBO) 1P + N 40 A 6 kA outgoer
[In] Rated Current	63 A (maximum)
[Ue] Rated Operational Voltage	240 V
Network Frequency	50 Hz
Total Number Of 18 Mm Modules	12
Cable Entry	2 knock-outs at left side 2 knock-outs at right side 5 knock-outs at top 5 knock-outs at bottom
Cable Cross Section	1...25 mm ²
Number Of Horizontal Rows	1
Type Of Rail	DIN
Comb Busbar And Distribution Block Compatibility	YES
Product Compatibility	Acti9 isolator Acti9 MCB Acti9 RCCB Acti9 RCBO

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Enclosure Mounting	Surface Flush
Number Of Ways	12 ways
Height	244 mm
Width	365 mm
Depth	93 mm
Net Weight	3.5 kg
Ip Degree Of Protection	IP43
Ik Degree Of Protection	IK08

Environment

Standards	IEC 61439-3
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.9 cm
Package 1 Width	36.5 cm
Package 1 Length	24.4 cm
Package 1 Weight	3.8 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	1
Package 2 Height	11 cm
Package 2 Width	37.8 cm
Package 2 Length	25.5 cm
Package 2 Weight	3.8 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	52
Package 3 Height	110 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	340 kg