

Bảng thông số sản phẩm

Thông số kỹ thuật



Momentary Switch, AvatarOn, 4A, 250V, 4gangs, Wine Gold

E8334PRL1_WG_C1

Main

Product Or Component Type	Switch
Device Application	Control
Load Type	Inductive Incandescent lamp Resistive Fluorescent lamp
Colour Tint	Wine gold
Colour Tint	Wine gold

Complementary

Device Presentation	Complete product
Rated Current	4 A at 250 V AC 50/60 Hz
Switch Function	Momentary
Number Of Gangs	4 gangs
Number Of Rocker	4
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Brass terminal
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator
Device Mounting	Surface Flush
Width	86 mm
Height	86 mm
Depth	34.2 mm
Embedding Depth	24.5 mm

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	35 °C
Operating Altitude	2000 m
Relative Humidity	0...95 %

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Environmental Characteristic	UV resistant
Standards	GB/T 16915.1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	122 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	960
Package 2 Height	990 cm
Package 2 Width	800 cm
Package 2 Length	600 cm
Package 2 Weight	148980 g

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Bao bì bền vững Minh bạch RoHS/REACH

Hiệu suất tài nguyên

✓

Sustainable Packaging

Hiệu suất sức khỏe

✓

Reach Free Of Svhc

✓

Toxic Heavy Metal Free

✓

Mercury Free

✓

RoHS Exemption Information

Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations