

Bảng thông số sản phẩm

Thông số kỹ thuật



Spacial S3HF H600xW400xD200 EMC-immunity IP55 RAL7035

NSYS3HF6420P

Main

Range	Spacial
Product Name	Spacial S3HF
Application	Industrial application
Category	Compact enclosure
Enclosure Nominal Height	600 mm
Enclosure Nominal Width	400 mm
Enclosure Nominal Depth	200 mm
Door Type	Plain
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door with lock 1 mounting plate

Complementary

Body Type	Single piece body
Number Of Doors	Front face: 1 door(s)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body: aluzinc
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 60529
Net Weight	13.8 kg

Environment

Electromagnetic Compatibility	EMC immunity
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55

Packing Units

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.0 cm
Package 1 Width	40.8 cm
Package 1 Length	61.3 cm
Package 1 Weight	13.8 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)
[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

- ✓

Mercury Free
- ✓

Rohs Exemption Information

Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations