

# Product data sheet

Specifications



## 9M SIDE PANEL PRISMA G IP30

01041

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Side panel
Accessory / Separate Part Category	Spare part Enclosure accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Wall-mounted enclosure
Mounting Location	Side
Number Of Vertical Modules [50 Mm]	9

### Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Textured epoxy polyester Glossy
Colour	White (RAL 9001)
Special Colour Options	Yes
Width	200 mm
Height	475 mm
Depth	180 mm
Net Weight	0.986 kg
Quantity Per Set	Set of 1

### Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07 IK08

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	21.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	68.000 cm
Package 1 Weight	1.055 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	32.500 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	76.000 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
---------------------------------	---

<b>Circularity Profile</b>	<a href="#">End of Life Information</a>
----------------------------	---