

Bảng thông số sản phẩm

Thông số kỹ thuật



Climasys Ultra thin resistance
heater low starting current 195W
240V 400x650mm

NSYCRS200W240V

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	195 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable length: 2 m

Complementary

Operating Position	Horizontal Vertical
Ambient Air Temperature For Operation	-60...70 °C
Temperature Setting Range	-40...70 °C
Material	Silicone rubber
Height	380 mm external:
Width	650 mm external:
Depth	1.6 mm external:
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed
Fixing Mode	By 4 screws
Mounting Support	Adhesive Velcro Telequick mounting plate Standard mounting plate DIN rail

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	43.0 cm
Package 1 Length	69.5 cm

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Package 1 Weight	1.13 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	150.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	47.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

 Mercury Free

 Rohs Exemption Information [Yes](#)

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations