


# Product data sheet

Specifications



## W400 ADJUSTABLE MODULAR DEVICE RAIL PRISMA P

03404

⚠ Discontinued on: Jan 20, 2022

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Rail
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P
Type Of Rail	Modular Adjustable
Installed Device	ComPact: fixed INS100 - control: direct front rotary handle - vertical installation ComPact: fixed INS160 - control: direct front rotary handle - vertical installation ComPact: fixed INS40 - control: direct front rotary handle - vertical installation ComPact: fixed INS63 - control: direct front rotary handle - vertical installation Acti 9: fixed modular device Multi9: fixed modular device Multi9: fixed NG125 without earth leakage protection - control: toggle ComPact: fixed INS125 - control: direct front rotary handle - vertical installation Acti 9: fixed modular device <= 40 A Multi9: fixed modular device <= 40 A ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle ComPact: fixed NSA125...160 - control: toggle

Poles Description	1 x 3P: fixed INS100 vertical installation 1 x 4P: fixed INS100 vertical installation 1 x 3P: fixed INS160 vertical installation 1 x 4P: fixed INS160 vertical installation 1 x 3P: fixed INS40 vertical installation 1 x 4P: fixed INS40 vertical installation 1 x 3P: fixed INS63 vertical installation 1 x 4P: fixed INS63 vertical installation 1 x 3P: fixed NG125 1 x 4P: fixed NG125 1 x 3P: fixed INS125 vertical installation 1 x 4P: fixed INS125 vertical installation 1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA 1 x 3P: fixed NSA125...160 1 x 4P: fixed NSA125...160
-------------------	--

### Complementary

Installation Description	Cubicle - width 400 mm depth 400 mm
Enclosure Nominal Height	2000 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Vertical Modules [50 Mm]	4 module(s): INS100, direct in 400 mm Widecubicle 5 module(s): INS100, direct in 400 mm Widecubicle 4 module(s): INS125, direct in 400 mm Widecubicle 5 module(s): INS125, direct in 400 mm Widecubicle 4 module(s): INS160, direct in 400 mm Widecubicle 5 module(s): INS160, direct in 400 mm Widecubicle 4 module(s): INS40, direct in 400 mm Widecubicle 4 module(s): INS63, direct in 400 mm Widecubicle 3 module(s): modular device <= 40 A, direct in 400 mm Widecubicle 4 module(s): modular device, direct in 400 mm Widecubicle 5 module(s): NG125 without earth leakage protection , direct in 400 mm Widecubicle 5 module(s): NG160 without earth leakage protection , direct in 400 mm Widecubicle 5 module(s): NG160 NA without earth leakage protection , direct in 400 mm Widecubicle 5 module(s): NSA125...160, direct in 400 mm Widecubicle
9 Mm Pitches	20
Quantity Per Set	Set of 1
Height	30 mm
Width	325 mm
Depth	325 mm
Net Weight	0.76 kg
Colour	Natural
Material	Metal

## Environment

Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---