


Product data sheet

Specifications



MOUNTING PLATE VIGI NSX/CVS TOGGLE - 3P 250A HORIZONTAL WIDTH 650

03411

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm
Installed Device	EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS100...160 with earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: fixed CVS100...160 horizontal installation 1 x 3P: fixed CVS250 horizontal installation 1 x 3P: fixed NSX100...160 horizontal installation 1 x 3P: fixed NSX250 horizontal installation
Number Of Vertical Modules [50 Mm]	3 module(s): CVS100...160 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS250 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX100...160 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX250 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS100...160 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): CVS250 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	650 mm
Height	141 mm
Net Weight	1.16 kg
Functional Unit	650 mm 400 mm Prisma P cubicle EasyPact CVS100...160 without fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS250 without fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX100...160 without fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 without fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS250 with fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 with fixed toggle horizontal 3P 1 direct 3 12.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	15.000 cm
Package 1 Length	58.000 cm
Package 1 Weight	1.150 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	20.000 cm
Package 2 Width	33.000 cm
Package 2 Length	61.000 cm
Package 2 Weight	9.950 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	128
Package 3 Height	95.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	161.120 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---