


Product data sheet

Specifications



M.PL.HZ.NS250 C/O MOT.OR UA/BA

03417

 **Discontinued on:** Jan 11, 2022

 **Discontinued**

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 600 mm
Installed Device	Source changeover: fixed BA controller - horizontal installation Source changeover: fixed NSX100...250 source changeover - control: remote control - horizontal installation Source changeover: fixed UA controller - horizontal installation
Poles Description	2 x 3P: fixed NSX100...250 source changeover horizontal installation 2 x 4P: fixed NSX100...250 source changeover horizontal installation
Number Of Vertical Modules [50 Mm]	4 module(s): BA controller, direct in 650 mm Widecubicle 8 module(s): NSX100...250 source changeover, direct in 650 mm Widecubicle 4 module(s): UA controller, direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	650 mm
Height	200 mm
Net Weight	3 kg
Functional Unit	650 mm 600 mm Prisma P cubicle source changeover BA controller fixed horizontal 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle source changeover NSX100...250 source changeover fixed remote control horizontal 3P 2 direct 8 12.5 mm 650 mm 400 mm Prisma P cubicle source changeover NSX100...250 source changeover fixed remote control horizontal 4P 2 direct 8 12.5 mm 650 mm 600 mm Prisma P cubicle source changeover UA controller fixed horizontal 1 direct 4 12.5 mm

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	11 cm
Package 1 Length	57 cm
Package 1 Weight	2.9 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts Product

Certifications & Standards

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)