


Product data sheet

Specifications

FR.PL.HZ.NS630 TOGGLE 3P



03651

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed EZC400 - control: toggle - horizontal installation EasyPact: fixed EZC630 - control: toggle - horizontal installation EasyPact: fixed CVS400 with earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS630 with earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: mounting plate support: CVS400 horizontal installation 1 x 3P: mounting plate support: CVS630 horizontal installation 1 x 3P: mounting plate support: EZC400 horizontal installation 1 x 3P: mounting plate support: EZC630 horizontal installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	500 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.8 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle EasyPact CVS400 without fixed toggle horizontal 3P 1 direct 4 650 mm 400 mm Prisma P cubicle EasyPact CVS630 without fixed toggle horizontal 3P 1 direct 4 650 mm 400 mm Prisma P cubicle EasyPact EZC400 fixed toggle horizontal 3P 1 direct 4 650 mm 400 mm Prisma P cubicle EasyPact EZC630 fixed toggle horizontal 3P 1 direct 4 650 mm 400 mm Prisma P cubicle EasyPact CVS400 with fixed toggle horizontal 3P 1 direct 4 650 mm 400 mm Prisma P cubicle EasyPact CVS630 with fixed toggle horizontal 3P 1 direct 4

Environment

Ip Degree Of Protection	IP30
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	802.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	22.5 cm
Package 2 Length	53.0 cm
Package 2 Weight	10.0 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	360
Package 3 Height	82.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	320.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---