


# Product data sheet

Specifications

## 4 HEXAGONAL SPACERS M6 H9



03195

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Hexagonal spacers
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle Prisma Prisma G front cover support upright Prisma Prisma PH cubicle Prisma Prisma iPM L enclosure Prisma Prisma iPM M enclosure
Cubicle-Device Connection	Earth bar: vertical by screws

### Complementary

Mounting Mode	By screws
Mounting Support	Functional uprights
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle Cubicle duct
Iso Thread	M6
Quantity Per Set	Set of 4
Height	9 mm
Net Weight	0.06 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	10.5 cm
Package 1 Length	15 cm
Package 1 Weight	60 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.501 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	200
Package 3 Height	30 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	12 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---