


# Product data sheet

Specifications



## PLAIN FRONT PLATE W300 3M

03813

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle
Type Of Front Plate	Plain
Installed Device	TeSys: fixed D or K contactors <= 40 A - horizontal installation
Poles Description	4 x 4P: modular rail support: D or K contactors <= 40 A horizontal installation

### Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	250 mm
Net Weight	0.38 kg
Quantity Per Set	Set of 1
Functional Unit	300 mm Prisma G floor-standing duct TeSys D or K contactors <= 40 A fixed horizontal 4P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys D or K contactors <= 40 A fixed horizontal 4P 4 direct 3 400 mm 400 mm Prisma P cubicle 3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	15.500 cm
Package 1 Length	26.000 cm
Package 1 Weight	360.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	16.600 cm
Package 2 Width	17.700 cm
Package 2 Length	27.600 cm
Package 2 Weight	3.850 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	320
Package 3 Height	48.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	149.760 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---