


Product data sheet

Specifications



MOUNTING PLATE VIGI NSX/CVS PLUGIN TOGGLE/ROT/MOT - 3P 630A HORIZONTAL WIDTH 650

03453

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: motor mechanism - horizontal installation EasyPact: fixed CVS400 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX630 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: motor mechanism - horizontal installation
Poles Description	1 x 3P: fixed CVS400 horizontal installation 1 x 3P: fixed CVS630 horizontal installation 1 x 3P: fixed NSX400 horizontal installation 1 x 3P: fixed NSX630 horizontal installation 1 x 3P: plug-in NSX400 horizontal installation 1 x 3P: plug-in NSX630 horizontal installation
Number Of Vertical Modules [50 Mm]	4 module(s): CVS400 without earth leakage protection , direct in 650 mm Widecubicle 4 module(s): CVS630 without earth leakage protection , direct in 650 mm Widecubicle 4 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle 4 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle 4 module(s): CVS400 with earth leakage protection , direct in 650 mm Widecubicle 4 module(s): CVS630 with earth leakage protection , direct in 650 mm Widecubicle 4 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle 4 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle 3 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	650 mm
Height	200 mm
Net Weight	2.5 kg
Functional Unit	650 mm 400 mm Prisma P cubicle EasyPact CVS400 without fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS630 without fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS400 with fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle EasyPact CVS630 with fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in toggle horizontal 3P 1 direct 3 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed motor mechanism horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in direct front rotary handle horizontal 3P 1 direct 4 12.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in motor mechanism horizontal 3P 1 direct 4 12.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	21 cm
Package 1 Length	58 cm
Package 1 Weight	2.61 kg
Unit Type Of Package 2	S04

Number Of Units In Package 2	9
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	24.1 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	108
Package 3 Height	105 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	301.2 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts Product

Certifications & Standards

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)