


Product data sheet

Specifications



Connection for vertical fixed INS-INV, 4P 1600A, on Linergy LGY

04482

⚠ Discontinued on: Jan 20, 2022

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Connection
Product Name	Prisma Prisma P enclosure
Accessory / Separate Part Category	Current distribution accessory
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

Complementary

Cubicle-Device Connection	Linergy busbar
Poles Description	4P
Installation Description	Cubicle - width 650 mm
Installed Device	ComPact: fixed INS630b...1600 - control: direct front rotary handle vertical installation ComPact: fixed INV630b...1600 - control: direct front rotary handle vertical installation
[Ie] Rated Operational Current	1600 A
[In] Rated Current	1600 A
Busbar Cross Section	80 x 10 mm
Net Weight	18.56 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle ComPact INS630b...1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 650 mm 400 mm Prisma P cubicle ComPact INV630b...1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	13 cm
Package 1 Length	58 cm
Package 1 Weight	18.57 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---