

Product data sheet

Specifications



Micro Pragma surface enclosure - IP30 - 1x6modules - reversible transparent door

10207

Main

Range	Micro Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	6
Nb Of Horizontal Rows	1
Type Of Door	Reversible Transparent
Width	140 mm
Height	165 mm
Depth	72 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	12
Total Number Of 18 Mm Modules	6
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Enclosure Material	Enclosure: self-extinguishing material
Internal Depth	66 mm
Colour	Enclosure: white (RAL 9003)
Market Segment	Small commercial

Environment

Standards	IEC 60695-2-1 IEC 60439-3 IEC 23-48 EN 60439-3
Fire Resistance	650 °C (30 s) conforming to IEC 60695-2-1
Ip Degree Of Protection	IP40 conforming to IEC 60529 (with installation of devices IP40 minimum)
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	7.500 cm
Package 1 Width	14.000 cm
Package 1 Length	16.500 cm
Package 1 Weight	230.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	24
Package 2 Height	24.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	6.130 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	36.520 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information