


Product data sheet

Specifications

Multi9 - comb busbar - 3L - 18 mm pitch - 12 modules - 100A



10287

Main

Range	Multi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	4 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	18 mm
Connector Type	Tooth
Distance Between Way	54 mm
Marking	L1 L2 L3
Insulation	Insulated
Device Presentation	Uncuttable
[Ie] Rated Operational Current	100 A at 40 °C
[Ue] Rated Operational Voltage	277 V AC Ph/N 480 V AC Ph/Ph
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	12 kV
Mounting Location	Top on tunnel type terminals
9 Mm Pitches	24
Width	216 mm
Colour	Light grey (RAL 7035)
Range Compatibility	Multi9 Multi9 C60SP

Environment

Standards	IEC 60947-2 GB 14048.2 UL 1077
Fire Resistance	960 °C (30 s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	5.5 cm
Package 1 Length	22.0 cm
Package 1 Weight	108.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	72
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.102 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile		No need of specific recycling operations