


Product data sheet

Specifications



TRANSPARENT DOOR 6R

08096

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G enclosure
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Enclosure Mounting	Flush with kit Surface
Type Of Door	Transparent
Ip Degree Of Protection	IP30

Complementary

Installation Description	Pack enclosure - width 555 mm
Door Opening Side	Reversible
Number Of Locks	1
Door Opening Angle	130 °
Number Of 18 Mm Modules Per Row	24
Total Number Of 18 Mm Modules	144
Number Of Vertical Modules [50 Mm]	21
Number Of Horizontal Rows	6
Enclosure Material	Handle: polyamide Glass Cover frame: treated sheet steel
Quantity Per Set	Set of 1
Height	1080 mm
Width	550 mm
Depth	22 mm
Net Weight	6.6 kg
Material	Glass
Surface Finish	Matt Smooth

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White (RAL 9001)
--------	------------------

Environment

Ik Degree Of Protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	59.0 cm
Package 1 Length	112.0 cm
Package 1 Weight	6.51 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	15
Package 2 Height	97.5 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	99.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile