

Product data sheet

Specifications



Defem - support hook - B39 - steel, electro-galvanized - 320/422

1149118

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

| | |
|---------------------------|--------------|
| Range | Defem |
| Product Or Component Type | Support hook |
| Device Short Name | B39 |

Complementary

| | |
|----------------------------------|--|
| Material With Surface Treatment | Steel (electro-galvanized) |
| Atmospheric-Corrosivity Category | C1 |
| Fixing Device Mounting | Suspended on threaded rod |
| Product Destination | Mesh tray 320 mm width Mesh tray 422 mm width |
| Height | 25 mm |
| Width | 290 mm |
| Net Weight | 30 kg / set of 100 |
| Depth | 49 mm |

Environment

| | |
|------------------------------|---|
| Environmental Characteristic | Heated facility with low exposure to corrosion hotels and offices |
|------------------------------|---|

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.5 cm |
| Package 1 Width | 4 cm |
| Package 1 Length | 29 cm |
| Package 1 Weight | 315 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|-----------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile | No need of specific recycling operations |