


Product data sheet

Specifications

CUT-OUT METAL GLAND PLATE W600 /G IP30



08871

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range Of Product	Prisma G
Range	Prisma
Range Compatibility	Prisma Prisma G enclosure
Product Or Component Type	Support gland plate
Accessory / Separate Part Category	Enclosure accessory
Product Compatibility	IP30 enclosure IP43 enclosure IP31 enclosure

Complementary

Enclosure/Cubicle Description	Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 600 mm
Material	Metal
Quantity Per Set	Set of 1
Width	600 mm
Depth	180 mm
Net Weight	0.75 kg
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Environment

Ip Degree Of Protection	IP30
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	14.3 cm
Package 1 Length	49 cm
Package 1 Weight	800 g
Unit Type Of Package 2	S04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	30
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	24.7 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	209.6 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---