


Product data sheet

Specifications

Multi9 - comb busbar - 1L - 18 mm pitch - 12 modules - 100A



10171

 **Discontinued on:** May 31, 2021

 **Discontinued**

Main

Range	Multi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	1L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	12 ways 1 L
Poles Configuration For 1 Way	1 x 1P
Connection Pitch	18 mm
Connector Type	Tooth
Distance Between Way	18 mm
Insulation	Insulated
Device Presentation	Uncuttable
[Ie] Rated Operational Current	100 A at 40 °C
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz conforming to UL 508
[Uimp] Rated Impulse Withstand Voltage	12 kV conforming to UL 508
Mounting Location	Top on tunnel type terminals
9 Mm Pitches	24
Width	216 mm
Colour	White (RAL 9001)
Range Compatibility	Multi9 Multi9 C60 C60 UL489

Environment

Standards	UL 508
Fire Resistance	960 °C (30 s) conforming to UL 508

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	9.5 cm
Package 1 Length	23.7 cm
Package 1 Weight	646 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	