

# Product data sheet

Specifications



## 103 x 225 mm plate - 2 openings

13142

### Main

Range Of Product	Kaedra
Product Or Component Type	Plate
Type Of Front Plate	With cut-outs
Accessory / Separate Part Type	Installation accessories
Socket Dimensions Compatible	1 gang 65 x 85 mm ofsocket-outlet 1 gang 90 x 100 mm ofsocket-outlet

### Complementary

Enclosure Material	Housing: self-extinguishing polymer
Net Weight	0.188 kg
Base Dimension	103 x 225 mm
Width	103 mm
Height	225 mm
Colour	Grey (RAL 7035)

### Environment

Standards	IEC 60309-2 IEC 60309-1
Fire Resistance	650 °C conforming to IEC 60695-2-11
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to IEC 62262

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	10.2 cm
Package 1 Length	22.5 cm
Package 1 Weight	144 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	11.6 cm
Package 2 Width	21.6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	27.5 cm
Package 2 Weight	1.27 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.24 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)