

# Product data sheet

Specifications



## Polinorma - horizontal wall bracket - PVC - 600 mm - grey

4321200

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range Of Product	Polinorma
Product Or Component Type	Horizontal bracket
Colour	Grey (RAL 7030)
Quantity Per Set	Set of 2

### Complementary

Permanent Permissible Load	110 kg
Product Destination	Cable tray H= 100 mm W= 600 mm
Mounting Support	Wall
Material	PVC (polyvinyl chloride)
Height	160 mm
Width	80 mm
Depth	660 mm

### Environment

Flame Retardance	V0
Standards	EN 60695-11-10 IEC 61537 UNE 23727
Ambient Air Temperature For Operation	-20...60 °C
Ik Degree Of Protection	IK10

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.500 cm
Package 1 Width	20.500 cm
Package 1 Length	68.000 cm
Package 1 Weight	1.245 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	9.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	20.500 cm
Package 2 Length	68.000 cm
Package 2 Weight	2.490 kg
Unit Type Of Package 3	BB2
Number Of Units In Package 3	2
Package 3 Height	9.500 cm
Package 3 Width	20.500 cm
Package 3 Length	68.000 cm
Package 3 Weight	2.490 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations