


# Product data sheet

Specifications



## Performa - mesh tray - electro-zinc - 70 mm x 100 mm x 3000 mm

4511210

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

Range Of Product	Performa
Product Or Component Type	Mesh tray
Quantity Per Set	12 m

### Complementary

Shape	U-shape
Material	Steel (electro-zinc)
Atmospheric-Corrosivity Category	C1
Longitudinal Wire Diameter	3.9 mm
Transversal Wire Diameter	3.9 mm
Cable Cross Section	5268 mm <sup>2</sup>
Standards	IEC 60068-2-75 IEC 61537 EN 12329 DIN 4102-12 EN 50102 EN/ISO 9227
Length	3 m
Height	75 mm
Width	100 mm
Height Compatibility	70 mm
Width Compatibility	100 mm
Surface Treatment Compatibility	Electro-zinc

### Environment

Ambient Air Temperature For Operation	-40...120 °C
Ik Degree Of Protection	IK10

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10 cm
Package 1 Length	100 cm
Package 1 Weight	876 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations