


# Product data sheet

Specifications



## Communicating opening voltage release MX, MasterPact NT/NW, 200/250V AC/DC, spare part

33036

### Main

Range	MasterPacT
Range Of Product	MasterPact NT MasterPact NW
Device Short Name	MX com XF com
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil Closing coil
Control Type	Communicating
[Uc] Control Circuit Voltage	200...250 V AC 50/60 Hz 200...250 V DC
Circuit Breaker Mounting Mode	Fixed Drawout
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW

### Complementary

Operating Threshold	0.7...1.1 x Un opening
Response Time	55 ms +/- 10 % for MasterPact NT 70 ms +/- 10 % for MasterPact NW 50 ms +/- 10 % for Compact NS630b...1600 50 ms +/- 10 % for Compact NS1600b...3200
Supply Holding Power	4.5 VA
Accessory / Separate Part Category	Spare part for MasterPact NT Spare part for MasterPact NW

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.2 cm
Package 1 Length	8.3 cm
Package 1 Weight	152.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	8.9 cm
Package 2 Width	18.5 cm
Package 2 Length	13.2 cm
Package 2 Weight	1.575 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	9.85 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>