

# Product data sheet

Specifications

## Thorsman - TST 4.2x25 - screw - hexagonal - set of 1000



3780221

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

### Main

Range Of Product	Thorsman
Product Or Component Type	Collar screw
Device Short Name	TST
Device Application	Wood fibreboard Sheet steel Plug
Screw Type	Fully threaded with twin thread
Tool Type	screwdriver magnetic socket
Quantity Per Set	Set of 1000

### Complementary

Screw Diameter	4.2 mm
Screw Length	25 mm
Shape Of Screw Head	Hexagonal
Screwdriver Shape	Philips No 2
Centring Collar Diameter	8.3 mm
Centring Collar Depth	10.1 mm
Material	Screw: hardened steel electroplated
Net Weight	0.0024 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	0.6 cm
Package 1 Length	2.6 cm
Package 1 Weight	2.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	6.0 cm
Package 2 Width	13.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	19.6 cm
Package 2 Weight	2.232 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations