


Product data sheet

Specifications



Polinorma - plate cover - 500 mm - grey

4311533

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Polinorma
Product Or Component Type	Cover
Colour	Grey (RAL 7030)
Quantity Per Set	6 m

Complementary

Fixing Mode	Snap-in
Material	PVC (polyvinyl chloride)
Product Destination	Cable tray H= 100 mm W= 500 mm
Thickness	6 mm
Width	500 mm
Length	3000 mm

Environment

Flame Retardance	V0
Standards	IEC 61537 EN 60695-11-10 UNE 23727
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP44
Ik Degree Of Protection	IK10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	50.5 cm
Package 1 Length	300 cm
Package 1 Weight	1.911 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	1.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	50.5 cm
Package 2 Length	300 cm
Package 2 Weight	11.466 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	252
Package 3 Height	91 cm
Package 3 Width	300 cm
Package 3 Length	120 cm
Package 3 Weight	501.572 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations