

# Product data sheet

Specifications



## Push button interface, C-Bus, 30 Series module, master

5031NMML

### Main

Range	C-Bus
Product Brand	Clipsal
Product Name	Series 30M
Product Or Component Type	Push-button interface
Device Application	Control
Colour	White
Switch Application	Load switching Dimming up/down control Timer Scene control Bell switch Shutter control Fan speed control Blind control

### Complementary

Range Compatibility	C-Bus
Dimmer Control	255 possible levels
Device Mounting	Wall mounted by Series 30M grid
[Ue] Rated Operational Voltage	15...36 V DC
Input Impedance	100 kOhm at 1 kHz
Local Signalling	LED (blue/orange) for status
Suitable Cable Type	Twisted unshielded pairs cable category 5e
Isolation Voltage	3.75 kV from C-Bus to mains
Communication Network Type	C-Bus
Module Type	Master
Control Type	Push-button
Depth	41 mm
Width	23 mm
Height	23 mm
Net Weight	0.013 kg
Material	Plastic
Starting Time	5 s
Module Configuration	Programmed with learn mode Programmed with C-Bus software

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Time Delay Range	1s...18h12m15s
Current Consumption	18 mA

## Environment

Ambient Air Temperature For Operation	0...45 °C
Relative Humidity	10...95 % non-condensing
Product Certifications	RCM
Standards	AS/NZS CISPR 15 AS/NZS CISPR 14-1 AS/NZS 60669.2.1

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	3 cm
Package 1 Length	10 cm
Package 1 Weight	52 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>