

# Product data sheet

Specifications



## Horizontal rear connection replacement kit, MasterPact NW40, 4 poles, fixed/drawout, 4000A, spare part

47971

### Main

|                                    |                            |
|------------------------------------|----------------------------|
| Range Of Product                   | MasterPact NW              |
| Product Or Component Type          | Rear connection            |
| Accessory / Separate Part Category | Connection accessory       |
| Range Compatibility                | Masterpact MasterPact NW40 |
| Poles Description                  | 4P                         |
| Mounting Mode                      | Fixed + drawout            |
| [In] Rated Current                 | 4000 A                     |

### Complementary

|                                    |            |
|------------------------------------|------------|
| Location Of Connection             | Rear       |
| Connection Position                | Horizontal |
| Connection Pitch                   | 115 mm     |
| Quantity Per Set                   | 4          |
| Accessory / Separate Part Category | Spare part |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 10.0 cm   |
| Package 1 Width              | 19.0 cm   |
| Package 1 Length             | 30.0 cm   |
| Package 1 Weight             | 4.06 kg   |
| Unit Type Of Package 2       | S03       |
| Number Of Units In Package 2 | 3         |
| Package 2 Height             | 30.0 cm   |
| Package 2 Width              | 30.0 cm   |
| Package 2 Length             | 40.0 cm   |
| Package 2 Weight             | 12.427 kg |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|                       |                            |   |
|-----------------------|----------------------------|---|
| ✓                     | Reach Free Of Svhc         |   |
| ✓                     | Toxic Heavy Metal Free     |   |
| ✓                     | Mercury Free               |   |
| ✓                     | Rohs Exemption Information | Yes   |
|                       |                            |   |
| Reach Regulation      |                            | <a href="#">REACH Declaration</a>   |
|                       |                            |   |
| Eu Rohs Directive     |                            | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
|                       |                            |   |
| China Rohs Regulation |                            | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |