


Product data sheet

Specifications



Thorsman - INKA-U161-3 - trunking base - 72 mm - natural - 2.5 m

5510020

Main

Range Of Product	Thorsman
Product Name	Thorsman INKA
Product Or Component Type	Installation trunking
Cabling Installation System	Trunking
Colour Tint	Natural
Quantity Per Set	10 m

Complementary

Compartment Partitioning	1 compartment
Trunking Dimension	161 x 72 mm
Trunking Material	Aluminium
Front Opening Size	80 mm
Fixing Mode	By brackets By screws
Material	Aluminium anodized
Length	2500 mm
Height	161 mm
Width	72 mm

Environment

Directives	73/23/EEC - low voltage directive 93/68/EEC - low voltage directive
Standards	EN 50085-1
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.100 cm
Package 1 Width	7.200 cm
Package 1 Length	250.000 cm
Package 1 Weight	6.725 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	PAL
Number Of Units In Package 2	48
Package 2 Height	80.200 cm
Package 2 Width	120.000 cm
Package 2 Length	256.000 cm
Package 2 Weight	360.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations