

# Product data sheet

Specifications



## Thorsman - INKA-ES161 A - stop end - 72 mm - optional colour

5510172

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

|                             |               |
|-----------------------------|---------------|
| Range Of Product            | Thorsman      |
| Product Name                | Thorsman INKA |
| Product Or Component Type   | Stop end      |
| Cabling Installation System | Trunking      |
| Colour Tint                 | Optional      |
| Quantity Per Set            | Set of 1      |

### Complementary

|                    |                         |
|--------------------|-------------------------|
| Trunking Material  | Aluminium               |
| Trunking Dimension | 161 x 72 mm             |
| Fixing Mode        | By screws               |
| Material           | Aluminium powder coated |
| Length             | 28 mm                   |
| Height             | 161 mm                  |
| Width              | 72 mm                   |

### Environment

|                                       |  |
|---------------------------------------|--|
| Directives                            | 93/68/EEC - low voltage directive<br>73/23/EEC - low voltage directive |
| Standards                             | EN 50085-1   |
| Ambient Air Temperature For Operation | -25...60 °C  |
| Ip Degree Of Protection               | IP20   |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 2.8 cm  |
| Package 1 Width              | 7.2 cm  |
| Package 1 Length             | 16.1 cm |
| Package 1 Weight             | 85.5 g  |
| Unit Type Of Package 2       | BB1     |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Number Of Units In Package 2 | 10        |
| Package 2 Height             | 11.5 cm   |
| Package 2 Width              | 13.5 cm   |
| Package 2 Length             | 20.5 cm   |
| Package 2 Weight             | 995 g     |
| Unit Type Of Package 3       | PAL       |
| Number Of Units In Package 3 | 2400      |
| Package 3 Height             | 95 cm     |
| Package 3 Width              | 80 cm     |
| Package 3 Length             | 120 cm    |
| Package 3 Weight             | 268.64 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |