


# Product data sheet

Specifications



## Thorsman - TDL-80 - mounting kit - low - white

5910110

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	Thorsman
Product Name	Thorsman TDL
Product Or Component Type	VDI mounting kit
Colour Tint	White (NCS 0502-Y81R)
Quantity Per Set	Set of 1

### Complementary

Mounting Support	Installation box c/c 60 mm Service carrier with 80 mm front Wall mounted
Material	PA (polyamide) ABS (acrylonitrile butadiene-styrene)
Surface Finish	Matt
Length	80 mm
Height	80 mm
Width	37 mm

### Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	5...40 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	10.3 cm
Package 1 Length	12.5 cm
Package 1 Weight	48.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	622.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations