

# Product data sheet

Specifications



716257

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

## Main

|                           |                    |
|---------------------------|--------------------|
| Range                     | Wibe               |
| Range Of Product          | Wibe Cable Ladders |
| Product Or Component Type | T-junction         |
| Device Short Name         | 56                 |

## Complementary

|                                 |                                      |
|---------------------------------|--------------------------------------|
| Inner Radius                    | 268 mm                               |
| Type Of Side Profile            | Closed profile                       |
| Type Of Rung                    | Perforated profile                   |
| Product Destination             | Reinforced cable ladder 300 mm width |
| Material With Surface Treatment | Steel, hot-dip galvanized            |
| Corrosion Class                 | C3/C4                                |
| Length                          | 1150 mm                              |
| Height                          | 150 mm                               |
| Width                           | 725 mm                               |
| Net Weight                      | 790 kg / set of 100                  |

## Environment

|                   |   |
|-------------------|---|
| Mounting Location | Area with high level of environmental corrosion, humidity and airborne pollution<br>industrial and coastal areas, chemical plants |
|-------------------|---|

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 15 cm  |
| Package 1 Width              | 73 cm  |
| Package 1 Length             | 115 cm |
| Package 1 Weight             | 7.9 kg |

## Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |