

# Product data sheet

Specifications



## PUSH BUTTON 600VAC 10A 30MM T-K

9001K1L1AH2

⚠ Discontinued on: Oct 11, 2019

⚠ Discontinued

### Main

|                                 |                         |
|---------------------------------|-------------------------|
| Range Of Product                | Harmony 9001K           |
| Product Or Component Type       | Illuminated push-button |
| Device Short Name               | K                       |
| Operator Profile                | Amber flush             |
| Operator Additional Information | Full guard in plastic   |

### Complementary

|                                |                            |
|--------------------------------|----------------------------|
| Bezel Material                 | Chromium plated metal      |
| Mounting Diameter              | 30 mm                      |
| Light Block Supply             | Via transformer            |
| Contacts Type And Composition  | 2 NO + 2 NC                |
| [Ie] Rated Operational Current | 10 A, AC-15<br>10 A, DC-13 |
| Contact Operation              | Standard                   |
| Device Presentation            | Complete product           |

### Environment

|                           |  |
|---------------------------|--|
| Product Certifications    | CSA LR 25490 class 3211 03<br>NEMA<br>UL listed file E42259 CCN NKCR<br>CE |
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |