


# Product data sheet

Specifications



## Wibe - adjustable bend W10S/ 40-600 - steel pre-galvanized white

729109

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

|                           |                  |
|---------------------------|------------------|
| Range                     | Wibe             |
| Product Name              | Wibe Cable Trays |
| Product Or Component Type | Adjustable bend  |
| Device Short Name         | W10              |

### Complementary

|                                 |   |
|---------------------------------|---|
| Operating Angle                 | 105...165 ° adjustable in steps of 7.5° |
| Direction Change Type           | Horizontal                              |
| Product Destination             | Cable tray H= 40 mm W= 600 mm           |
| Mounting Mode                   | Push-in                                 |
| Fixing Mode                     | By bolt<br>By locking plug              |
| Material With Surface Treatment | Steel, pre-galvanized white             |
| Corrosion Class                 | C2                                      |
| Height                          | 40 mm                                   |
| Width                           | 597 mm                                  |
| Net Weight                      | 380 kg / set of 100                     |

### Environment

|                   |   |
|-------------------|---|
| Mounting Location | Partly outdoor environment with low exposure to corrosion ware-houses and parking garages |
|-------------------|---|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 0.1 cm |
| Package 1 Width              | 99 cm  |
| Package 1 Length             | 67 cm  |
| Package 1 Weight             | 3.8 kg |

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |